



Lupolen 2427 H

Polyethylene, Low Density

Product Description

 $\textit{Lupolen} \ \textbf{2427} \ \textbf{H} \ \textbf{is an additivated, low density polyethylene. It contains an antioxidant, slip and}$ anti-blocking agent. It is delivered in pellet form.

Foodlaw compliance information about this product can be found in separate product

This product is not intended for use in medical and pharmaceutical applications.

Product Characteristics

Status Commercial: Active

ISO Test Method used

Availability Europe, Asia-Pacific, Africa-Middle East

Processing Methods Blown Film, Cast Film

Unspecified Antiblocking, Low Friction, Opticals, Good Features

Processability, Unspecified Slip

Typical Customer Applications Bags & Pouches, Blown Film, Cast Film, Film, Food

Packaging Film, Shrink Film

Typical Properties	Method	Value Unit
Physical		
Density	ISO 1183	0.924 g/cm ³
Melt flow rate (MFR) (190°C/2.16kg)	ISO 1133	1.9 g/10 min
Mechanical		
Dart drop impact (50µm, Blown Film)	ASTM D 1709	110 g
Tensile Modulus	ISO 527-1, -2	260 MPa
Tensile Stress at Yield	ISO 527-1, -2	11.0 MPa
Tensile Strength	ISO 527-1, -3	
		25.0 MPa
Note: MD		
		21.0 MPa
Note: TD		
Tensile Strain at Break	ISO 527-1, -3	050.04
Note: MD		250 %
Note. MD		600 %
Note: TD		000 70
Thermal		
Vicat softening temperature (A50 (50°C/h 10N))	ISO 306	94.0 °C
Melting Temperature	ISO 3146	111 °C
Optical		
Haze (50µm)	ASTM D 1003	<9 %
Gloss	ASTM D 2457	
(20°, 50µm)		>50
(60°, 50μm)		>100
Film		
Melt Temperature		160 to 200 °C

Additional Properties

Film properties tested using 50 μm thickness blown film extruded at a melt temperature of 180°C and a blow-up ratio of 1:2.5.

Natural Silica, ISO 3451-1: 0.1%

Erucamide, DIN 51454: 0.05%

Failure Energy, DIN 53373, 50 µm: 4 J/mm

Coefficient of Friction, ISO 8295: <20%

Recommended Film Thickness: 20 to 60 µm

Typical properties; not to be construed as specifications

Further Information

Lupolen 2427 H

Conveying equipment should be designed to prevent production and accumulation of fines and dust particles that are contained in polymer resins. These particles can under certain conditions pose an explosion hazard. We recommend the conveying system used is equipped with adequate filters, is operated and maintained that no leak develops and adequate

grounding exists at all times

Health and Safety:

The resin is manufactured to the highest standards but, special requirements apply to certain applications such as food end-use contact and direct medical use. For specific information on regulatory compliance contact your local representative

Workers should be protected from the possibility of skin or eye contact with molten polymer. Safety glasses are suggested as a minimal precaution to prevent mechanical or thermal injury

Molten polymer may be degraded if it is exposed to air during any of the processing and offline operations. The products of degradation have an unpleasant odour. In higher concentrations they may cause irritation of the mucus membranes. Fabrication areas should be ventilated to carry away fumes or vapours. Legislation on the control of emissions and pollution prevention must be observed. If the principles of sound manufacturing practice are adhered to and the place of work is well ventilated, no health hazards are involved in processing the resin.

The resin will burn when supplied with excess heat and oxygen. It should be handled and stored away from contact with direct flames and/or ignition sources. In burning the resin contributes high heat and may generate a dense black smoke. Starting fires can be extinguished by water; developed fires should be extinguished by heavy foams forming an aqueous or polymeric film. For further information about safety in handling and processing please refer to the Material Safety Data Sheet.

The resin is packed in 25 kg bags or in bulk containers protecting it from contamination. If it is stored under adverse conditions, i. e. if there are large fluctuations in ambient temperature and the atmospheric humidity is high, moisture may condense inside the packaging. Under these circumstances, it is recommended to dry the resin before use. Unfavourable storage conditions may also intensify the resin's slight characteristic odour.

The resin is subjected to degradation by ultra-violet radiations or by high storage temperatures. Therefore the resin must be protected from direct sunlight, temperatures above 40°C and high atmospheric humidity during storage. The resin can be stored over a period of more than 3 months without significant changes in the specified properties, appropriate storage conditions provided. Higher storage temperatures reduce the storage time

The information submitted is based on our current knowledge and experience. In view of the many factors that may affect processing and application, these data do not relieve processors of the responsibility of carrying out their own tests and experiments; neither do they imply any legally binding assurance of certain properties or of suitability for a specific purpose. The data do not relieve the customer from his obligation to control the resin upon arrival and to complain about faults. It is the responsibility of those to whom we supply our products to ensure that any proprietary rights and existing laws and legislation are observed

© LyondellBasell Industries Holdings, B.V. 2012

LyondellBasell markets this product through the following entities:

- Equistar Chemicals, LP
- Basell Sales & Marketing Company B.V.
- Basell Asia Pacific Limited
- Basell International Trading FZE
- LyondellBasell Australia Pty Ltd

For the contact details of the LyondellBasell company selling this product in your country, please visit http://www.lvondellbasell.com/

Before using a product sold by a company of the LyondellBasell family of companies, users should make their own independent determination that the product is suitable for the intended use and can be used safely and legally. Seller Makes no Warranty; express or implied (including any warranty of merchantability or fitness for a particular purpose or any warranty) other than as separately agreed to by the parties in a contract.

This product(s) may not be used in:
(i) any U.S. FDA Class I, Health Canada Class I, and/or European Union Class I medical devices, without prior notification to Seller for each specific product and application; or (ii) the manufacture of any of the following, without prior written approval by Seller for each specific product and application: U.S. FDA Class II medical devices; Health Canada Class II or III medical devices; European Union Class II medical devices; or any equivalent U.S. FDA, Health Canada, or European Union regulations pertaining to medical devices; packaging in direct contact with a pharmaceutical active ingredient and/or dosage form; and tobacco-related products and applications. This product(s) may not be used in the manufacture of any of the following applications: U.S. FDA Class III medical devices; Health Canada Class IV medical devices; European Class III medical devices; applications involving permanent implantation into the body; life-sustaining medical applications; and lead, asbestos or MTBE related applications. All references to the U.S. FDA, Health Canada and European Union regulations include another country's equivalent regulatory classification.

Users should review the applicable Material Safety Data Sheet before handling the product.

Addhere, Adflex, Adstif, Adsyl, Akoafloor, Akoalit, Alathon, Alkylate, Amazing Chemistry, Aquamarine, Aquathene, Arconate, Arcopure, Arcosolv, Arctic Plus, Arctic Shield, Avant, Catalloy, Clyrell, CRP, Crystex, Dexflex, Duopac, Duoprime, Explore & Experiment, Filmex, Flexathene, Glacido, Hifax, Histif, Crystex, Dexirex, Duopat, Duoprime, Expirite & Experiment, Filmex, Flexatherie, Glacido, Hilax, Histil, Hostacom, Hostalen, Ideal, Integrate, Koattro, LIPP, Lucalen, Luflexen, Lupolen, Lupolex, Luposim, Lupostress, Lupotech, Metocene, Microthene, Moplen, MPDIOL, Nerolex, Nexprene, Petrothene, Plexar, Polymeg, Pristene, Proofflex, Pro-Fax, Punctilious, Purell, SAA100, SAA101, Sequel, Softell, Spherilene, Spheripol, Spherizone, Starflex, Stretchene, Superflex, TBAc, Tebol, T-Hydro, Toppyl, Trans4m, Tufflo, Ultrathene, Vacido and Valtec are trademarks owned or used by the LyondellBasell family of companies

Adsyl, Akoafloor, Akoalit, Alathon, Aquamarine, Arconate, Arcopure, Arcosolv, Arctic Plus, Arctic Shield, Avant, CRP, Crystex, Dexflex, Duopac, Duoprime, Explore & Experiment, Filmex, Flexathene, Hifax, Hostacom, Hostalen, Ideal, Integrate, Koattro, Lucalen, Lupolen, Microthene, Moplen, MPDIOL, Nexprene, Petrothene, Plexar, Polymeg, Pristene, Pro-Fax, Punctilious, Purell, Sequel, Softell, Spheripol, Spherizone, Starflex, Tebol, T-Hydro, Toppyl, Tufflo and Ultrathene are registered in the U.S Patent and Trademark Office.

Release Date: 09 Apr 2013